

## **CIP – SERIES CLEAN-IN-PLACE SYSTEMS**

**AXEON®** Clean-In-Place Systems (CIP) are mobile skids used for cleaning membranes without removing them from the reverse osmosis system. The CIP systems are designed to be easily integrated with any of the AXEON X–Series or M–Series reverse osmosis models. However, these CIP systems are also engineered as standalone systems that are compatible with any manufacturer's membrane system.

**AXEON Clean-In-Place** vary in size according to the number of membrane vessels that are to be cleaned in parallel, which is determined by the number of vessels in the first stage of the reverse osmosis skid. A centrifugal pump provides the recirculation flow and pressure recommended by the membrane manufacturer. A built-in recycle loop allows for mixing of cleaning agents prior to use and tank level switches to protect the pump. Options include an immersion heater and a pH monitor.



AXEON also offers C-Series Membrane Cleaners for use with **AXEON Clean-In-Place Systems**. C-Series Cleaners are compatible with all brands of reverse osmosis, nanofiltration and ultrafiltration membranes.

## **FEATURES**

- On/Off Switch
- Pentair® 4.5 x 20" Housing (CIP-20 and CIP-40)
- Shelco Multi-Cartridge Housing (CIP-60 and CIP-100)
- AXEON SDF-Series 5 Micron Sediment Filter
- AXEON 316L Stainless Steel Pressure Gauges
- SCH 80 PVC Piping with Unions
- Mixing Loop with Valve
- Solution Tank (Polyethylene)

- Tank Level Switches
- Temperature Gauge
- AXEON Flow Meter
- 316L Stainless Steel Pump with TEFC Motor
- Hose Kit
- Caster Wheels

## **OPTIONS**

- Stainless Steel Immersion Heater
- pH Monitor

## **SPECIFICATIONS**

| Cleaning<br>System Model | Inlet Outlet (in) | Tank Size<br>(gal / ltr) | Flow Rate<br>(gpm / lpm) | Motor (HP) | Approximate Dimensions <sup>A</sup> L x W x H (in / cm) | Weight (lb / kg) |
|--------------------------|-------------------|--------------------------|--------------------------|------------|---|------------------|
| CIP – 20                 | 1.00              | 50 / 189                 | 20 / 75.70               | 2          | 42 x 27 x 55 / 107 x 69 x 140                           | 300 / 136        |
| CIP – 40                 | 1.50              | 100 / 378                | 40 / 151.40              | 2          | 62 x 35 x 65 / 158 x 89 x 165                           | 550 / 249        |
| CIP - 60                 | 2.00              | 200 / 757                | 60 / 227.12              | 5          | 64 x 40 x 73 / 163 x 102 x 185                          | 600 / 272        |
| CIP – 100                | 2.00              | 200 / 757                | 100 / 378.54             | 7.5        | 64 x 40 x 73 / 163 x 102 x 185                          | 650 / 295        |

A. Does not include operating space requirements.

